


ATLAS HYDRO



ATLAS HYDRO



P: Planomiller type - fixed portal

Atlas Hydro is a range of heavy duty medium and large size vertical milling centers with hydrostatic guideways, suitable for machining large components. Their design ensures maximum machining accuracy and high productivity, with great stability during operations. As all INNSE-BERARDI machines, also the ATLAS HYDRO machines are designed, sized and created using the FEM (Finite Element Method). The flexible, modular design offers two different configurations:

P: Planomiller type - fixed portal

G: Gantry type - lower rails

GU: Gantry type - upper rails

A complete range of advanced milling attachments provides the optimum solution for each user's application requirements.



G: Gantry type - lower rails




GU: Gantry type - upper rails

ATLAS HYDRO		
Distance between columns	mm	3.200 up to 10.000
RAM vertical travel (Z-axis)	mm	1.500 up to 4.000
RAM section	mm	550 x 550 - 630 x 630 - 680 x 680
Spindle power	kW	60 up to 110
Torque	Nm	up to 9.000
Axis		3+2 or 5
W-axis		fixed or moving crossrail

VERTICAL TURNING TABLES

Both, Alas Vision as well as Atlas Hydro can be equipped optionally with Turning Tables for Turning, Boring, Milling, Turn-Milling and Grinding. The full range is featuring hydrostatic main bearings. A complete range of advanced attachments provides the optimum solution for the different application requirements.




The modular design covers a broad range of different sizes:

Max. turning diameter	mm	up to 9.000
Turning table diameter	mm	up to 8.000
Turning table load	ton	up to 4.000
Turning table speed	rpm	up to 200
Turning table power	kW	up to 200



MAIN MARKETS



Innse-Berardi S.p.A.
Via Attilio Franchi, 20
25127 Brescia
Italy
Tel. +39 030 37061
sales@innse-berardi.com



www.innse-berardi.com

